Manual Supplement

Manual Title:1760 UsersPrint Date:June 2006Revision/Date:2, 5/10

Supplement Issue:1Issue Date:2/11Page Count:1

This supplement contains information necessary to ensure the accuracy of the above manual. This manual is distributed as an electronic manual on the following CD-ROM:

CD Title:	1760
CD Rev. & Date:	5, 7/2010
CD PN:	2583518



Change #1, 57261, 57516

On page 1-7, replace the first Figure with the following:

POWER SUPPLY 🛕 👰 🤇 🤅 🗴 🌋	
300 V CAT III	
NOMINAL 100-240 V ~ 50/60 Hz / 100-350 V	
OPERATING 83-264 V~ 45-65 Hz / 100-375 V	
35 W / 70 VA	
NO USER SERVICEABLE PARTS INSIDE	

On page 5-3, under *General Specifications*, replace the Power Supply with the following:

Power Supply Nominal	100 to 240 V ac, 50/60Hz, 100 to 350Vdc
Power Supply Operating	83 to 264 V ac, 45 to 65 Hz, 100 to 375Vdc, 35W/70 VA

On page 6-5, under *Flexible Current Probes for AC*, replace the Model No. Product No. column with:

Model No. Product No.
TPS FLEX 18-TF 3889490
TPS FLEX 24-TF 3889503
TPS FLEX 36-TF 3889515

On page 6-18, under *General Specification*, add the Measurement head cross section specifications and replace Weight, and Order-number with:

Measurement head cross section:	8 mm (0.3 in)
Weight:	Approx. 0.3 kg (0.66 lb)
Order-number:	3889490

On page 6-21, under *General Specification*, add the Measurement head cross section specifications and replace Weight, and Order-number with:

Measurement head cross section:	8 mm (0.3 in)
Weight:	Approx. 0.35 kg (0.66 lb)
Order-number:	3889503

On page 6-25, under *General Characteristics*, add the Measurement head cross section specifications and replace Weight, and Order-number with:

Measurement head cross section:	8 mm (0.3 in)
Weight:	Approx. 0.4 kg (0.88 lb)
Order-number:	3889515